DXB-S100

Single-workbench measuring equipment, the workbench can be placed directly on the desk for use.

Suitable user groups: scientific research institutions, laboratories and other enterprises and institutions with a wide variety of crystals, and sapphire watch mirror factories.

Corresponding crystals: small size crystals, sapphire crystal balls after removing the ingot, and various other single crystal materials.

- · Equipment is single-workbench.
- · The equipment is divided two parts: upper casing(work bench) and lower casing (electrical box).
- · Measure the angle of the end face of the ingot/wafer or OF flat crystal orientation.
- · Anual measurement and manual peak determination.
- · There are also a variety of sample stages, suitable for crystals of special sizes and special measurement requirements.

 \bowtie









Item	Specifications
Crystal Diameter	(Client Information)
Crystal thickness	(Client Information)
Measuring Angle	0~50°
Accuracy	±30" or ±15"





